

Product Information NFP-41

FOOD

Level Detector with integrated Temperature Sensor NFP-41



Application / Specified Usage

· Level detection and temperature measurement in one device

Application Examples

- · Dry running and temperature protection in pipes
- · Level detection and temperature measurement in vessels

Hygienic Design / Process Connection

- · Hygienic process connection with CLEANadapt
- · Conforming to 3-A Sanitary Standard for versions with DIRECTadapt
- · All wetted materials are FDA-conform
- · Sensor completely made of stainless steel
- · Complete overview of process connections: see order code
- The Anderson-Negele CLEANadapt system offers a flow-optimized, hygienic and easily sterilizable installation solution for sensors.

Features

- · CIP-/SIP-cleaning up to 143 °C / max. 120 minutes
- · Level detection and temperature measurement in one measurement point
- · Available with or without integrated electronic

Options / Accessories

- · Integrated temperature and level electronic (MPU-4, MNV-1)
- · Readymade connecting cable for M12 plug

Communication





FOOD Specification

2

Specification NFP-41		
Process connection	conforming to 3-A	CLEANadapt G1/2"
Insertion length		29 mm
Material	head protection tube M12 plug insulator	stainless steel 1.4301 (AISI 304) stainless steel 1.4404 (AISI 316L) stainless steel 1.4301 (AISI 304) PEEK (FDA approval number 21CFR177.2415)
Sensing resistor	acc. ITS 90	1x Pt100 class A
Protection class		IP 69 K
Temperature range	ambient sensor tip CIP/SIP	-50+80 °C -50+150 °C up to 143 °C/120 min
Operating pressure		max. 10 bar
Electrical connection	plug-in connection	M12 plug, 5 pin
Thread size G1/2"	Sealing system PEEK	10 Nm torque max.
Level Module MNV-1		
Temperature	operating storage	-10+80 °C -20+90 °C
Humidity	without condensate	095 %
Supply		1536 V DC
Sensor measurement		free of DC voltage
Sensitivity	MNV-1	0.1; 1; 10; 100 kΩ selectable
Output	short-circuit-proof	active 50 mA
Delay	fix	0.5 s
Switching logic	MNV-1	via jumpers (full/empty selectable)
Transmitter MPU-4		
Temperature ranges	standard	-10+40; 050 °C / 100 °C / 150 °C
Accuracy		< ±0.25 % (range 0150 °C)
Temperature drift	zero, span	< 0.01 %/K
Electrical connection	supply	835 V DC
Output	analog	420mA
Temperature range	ambient storage	-40+85 °C -40+120 °C

Accuracy classes of temperature sensors Tolerances for Pt100 acc. to DIN EN 60751						
Pt100	A 1/3 B 1/10 B					
0°C/100Ω	±0.15 K / ±0.06 Ω	±0.10 K / ±0.04 Ω	±0.03 K / ±0.01 Ω			
100 °C / 138.5 Ω ±0.35 K / ±0.13 Ω ±0.27 K / ±0.10 Ω ±0.08 K / ±0.03 Ω						

0...98 %

Humidity

without condensation

Sensor tip diameter and response time

All temperature sensors are available with smaller sensor tips, to ensure a shorter response time. The below-mentioned times were measured by emersing a temperature sensor from room temperature into boiling water.

Sensor tip Ø 3 mm Response time: $t_{50} \le 0.5 \text{ s}$ 90 %-time: $t_{90} \le 1.5 \text{ s}$

Mounting Instruction

- · Take attention of the maximal torque when you build in the sensor!
- · To guarantee a safe function, take a look on a good electrical connection between process connection of the sensor and the pipe or vessel.
- · Do not use any kind of sealing band like e.g. TEFLON tape!
- · Using the sensor in pipes for dry running protection, take care that the electrode will emerge if the pipe runs out. We propose to install the sensor in vertical pipes.
- · Vessel resp. pipe wall must be made of steel!
- Please mounting and demounting the sensor, please use the spanner flat only! Do not use the connecting head!
- · Do not shorten the electrode!

General Operating Manual


· Mount the sensor into the fitting and perform wiring according to connection figures.


Startup the level module MNV-1


- Connecting to the voltage supply
- · Setup the switching logic: see figure
- · Select the lowerst sensitivity (0.1 k Ω).
- Wetting the electrode with the medium with the lowerst conductivity
- · If the output is switching, the setup is finished.
- If the output is not switching, increase the sensitivity until the output is switching. Setup is finished.


Level transmitter MNV-1C


- 1: LED sensor (lights up when the sensor is immersed, independent of the switching function)
- 2: Terminal block
- 3: Full/empty jumper
- 4: Sensitivity jumper

















Weld-in sleeves					
CLEANadapt G1/2"					
	Ø30 G1/2"	#30 G1/2" G1/2"	#30 G1/2" #30 919 945	#29 G1/2"	#30 G1/2" #355
	Cylindrical sleeve	Cylindrical sleeve with leakage hole	Weld-in sleeve with collar	Cylindrical sleeve with weld-in ring	Weld-in ball
	EMZ-132 * (for vessels)	EMZ-131 * (for vessels with leak monitor)	EMK-132 * (for thick-walled vessels)	EMS-132 * (for installation on pulled-out pipes)	KEM-132 * (for sloped installation)

 $^{^{*}}$ Deliverable with material 1.4435 and 3.1 inspection certificate on request.

5

Adapter to standard process connections						
CLEANad G1/2"	apt					
Diamete	r	Milk pipe (DIN 11851)	Tri-Clamp	Varivent-Inline	Tri-Clamp with tell-tale hole	DRD (press ring optional)
DN10		-	-	AMV-132/DN10	AMC-131/DN10	AMK-132/DN50
DN15		-	AMC-132/DN10	AMV-132/DN10	AMC-131/DN10	AMK-132/DN50
DN20		AMK-132/DN20	AMC-132/DN10	-	AMC-131/DN10	AMK-132/DN50
DN25	1"	AMK-132/DN25	AMC-132/DN25	AMV-132/DN25	AMC-131/DN25	AMK-132/DN50
DN32		AMK-132/DN32	AMC-132/DN25	AMV-132/DN25	AMC-131/DN25	AMK-132/DN50
DN40	11/2"	AMK-132/DN40	AMC-132/DN25	AMV-132/DN40	AMC-131/DN25	AMK-132/DN50
DN50	2"	AMK-132/DN50	AMC-132/DN50	AMV-132/DN40	AMC-131/DN50	AMK-132/DN50
	21/2"	AMK-132/DN65	AMC-132/2½"	AMV-132/DN40	AMC-131/2½"	-
DN65		AMK-132/DN65	AMC-132/DN65	AMV-132/DN40	AMC-131/DN65	AMK-132/DN50
	3"	-	AMC-132/DN65	AMV-132/DN40	AMC-131/DN65	-
DN80		AMK-132/DN80	AMC-132/DN80	AMV-132/DN40	AMC-131/DN80	AMK-132/DN50
DN100		AMK-132/DN100	-	AMV-132/DN40	AMC-131/DN100	AMK-132/DN50

Adapter to standard process connections









Diamete	r	APV-Inline	SMS	BioControl	
DN20		-	AMK-132/20	-	
DN25	1"	-	AMK-132/25	-	
DN32		-	AMK-132/32	-	
DN40	11/2"	AMA-132	AMK-132/40	AMB-50/½" and AMB-65/½" from DN40 up to DN100	
DN50	2"	AMA-132	AMK-132/50		
DN65	21/2"	AMA-132	AMK-132/65		
DN80		AMA-132	AMK-132/80		
DN100		AMA-132	AMK-132/100	•	

Adapter G1/2" to other thread sizes and accessories

G1/2"












Adapter	Adapter	Adapter	Adapter	Blind plug
AMG-1 (CLEANadapt G1" to CLEANadapt G1/2")	AMG-132 (Standard thread G1" to CLEAN- adapt G1/2")	AMG-132 / 3/4" (Standard thread G3/4" to CLEAN-adapt G1/2")	AMG-132 / 1 ¹ / ₄ " (Standard thread G1 ¹ / ₄ " to CLEAN-adapt G1/2")	BST-130 (to close a CLEANadapt G1/2" measurement point)





Dimensions table EHG-DIN2 / 1/2"					
Туре	DN	L	A	Da x W	
EHG-DIN2-25 / 1/2"	25	100	15	29 x 1.5	
EHG-DIN2-40 / 1/2"	40	120	22	41 x 1.5	
EHG-DIN2-50 / 1/2"	50	140	29	53 x 1.5	
EHG-DIN2-65 / 1/2"	65	160	38	70 x 2.0	
EHG-DIN2-80 / 1/2"	80	180	46	85 x 2.0	
EHG-DIN2-100 / 1/2"	100	200	55	104 x 2.0	
EHG-DIN2-125 / 1/2"	125	375	69,5	129 x 2.0	
EHG-DIN2-150 / 1/2"	150	450	82,0	154 x 2.0	

Transport / Storage



- · No outdoor storage
- · Dry and dust free
- · Not exposed to corrosive media
- Protected against solar radiation
- · Avoiding mechanical shock and vibration
- · Storage temperature -55 °C...+90 °C
- · Relative humidity max. 98 %

Cleaning / Maintenance



 In case of using pressure washers, dont't point nozzle directly to electrical connections!

Note on CE



- · Applicable directives:
- Electromagnetic Compatibility Directive 2014/30/EU
- Compliance with the applicable EU directives is identified by the CE label on the product.
- The operating company is responsible for complying with the guidelines applicable to the entire installation.

Conventional Usage



- · Not suitable for applications in explosive areas.
- Not suitable for applications in security-relevant equipments (SIL).

Reshipment



- Sensors shall be clean and must not be contaminated with dangerous media!
- Use suitable transport packaging only to avoid damage of the equipment!

Standards and Guidelines



 You have to comply with applicable regulations and directives.

Disposal



- Electrical devices should not be disposed of with household trash. They must be recycled in accordance with national laws and regulations.
- Take the device directly to a specialized recycling company and do not use municipal collection points.

Conditions for a measuring point according to 3-A Sanitary Standard 74-06 and EHEDG guidelines



- · The sensors NFP-41 conforming to the 3-A Sanitary Standard and the EHEDG guidelines.
- · Only approved in combination with the CLEANadapt build-in system (EMZ, EMK, EHG) or in combination with process connections AMC and AMV.
- · Using the weld in sleeve EMZ, EMK the weld must comply to the requirements of the current 3-A Sanitary Standard and the EHEDG guidelines.
- · Mounting position, self draining and the position of the leackage hole must be in accordance to current 3-A Sanitary Standard and the EHEDG guidelines.

Order Cod	e				
NFP-41					
	Sensor leng	th			
	015	(Sensor length	n in mm)		
		Electrical con	nection		
		M12	(M12 plug)		
			Transmitter X MNV MNV/MPU		evel transmitter) evel and temperature transmitter)
				Measureme	nt range temperature transmitter
V	•	*	*	-1040 050 0100 0150	(range -10+40 °C) (range 0+50 °C) (range 0+100 °C) (range 0+150 °C)
NFP-41/	015/	M12/	MNV/MPU/	0150	

Accessories

PVC-cable with M12-connection made of 1.4305, IP 69 K, unshielded M12-PVC / 5-5 m PVC-cable 5 pin, length 5 m PVC-cable 5 pin, length 10 m PVC-cable 5 pin, length 10 m PVC-cable 5 pin, length 25 m PVC-cable with M12-connection, brass nickel-plated, IP 67, shielded M12-PVC / 5G-5 m PVC-cable 5 pin, length 5 m

 M12-PVC / 5G-5 m
 PVC-cable 5 pin, length 5 m

 M12-PVC / 5G-10 m
 PVC-cable 5 pin, length 10 m

 M12-PVC / 5G-25 m
 PVC-cable 5 pin, length 25 m

Programming adapter

MPU-P 9701 Programming adapter for MPU-4, MPU-H and MPU-M



